SORT LIFT® Elevating sound

In order for any hi-fi system to perform at its highest level, it must be built upon a solid, sonic foundation. As a company, Nordost has applied this notion to all of our products, ranging from cables, to power products, to resonance control devices, allowing our customers to yield the best results from the components they already own. The Sort Lift[®] is no exception.

Nordost's Sort Lift[®] is the preeminent cable support in the consumer electronics industry, and is the latest addition to our Sort System. By utilizing a patent pending floating spring design, the Sort Lift[®] enhances the sonic performance of loudspeaker cables, power cords, and interconnects, by minimizing the points of contact that cables make with the ground and reducing boundary effects, without negatively affecting the resonant properties of the cables themselves.

The Sort Lift[®] is composed of two integral components: the base and the springs. The base is a stable, anodized, aluminum disk, designed to inhibit any transference of electrical charge from the floor to the cable and eliminate static build-up on the dielectric itself. This base supports the proprietary Floating Spring System. The Floating Spring System uses a flexible, titanium alloy spring-wire, which makes up both the support wings and tension wire supports. In both elements, the alloy wire is coated in FEP, mirroring the design of Nordost cables and making the supports an extension of the cable jacket, eliminating any electrical interference, while allowing the cables to maintain their natural resonance properties.

Sort Lifts[®] are provided in packs of two. They are intended to be spaced between 0.5 and 1 meter apart in distance, so that the cable does not come in contact with the floor. The spacing may depend on the weight and flexibility of the cable being supported.

ORT LIFT



While designed to be used primarily with Nordost cables, any audio cable will benefit from using the Sort Lift[®]. Noticeable effects include an elevated sound stage, improved dynamic range, increased detail in low frequency reproductions and more natural timbre to the sound.

- Proprietary Floating Spring System uses titanium alloy and FEP coating
- Anodized aluminum base
- Reduces boundary effects and electrical interference
- Inhibits transference of electrical charge and rids the dielectric of static build-up
- Elevates sound stage, improves dynamic range, and increases detail in low frequency reproductions

ORTIN



MAKING THE CONNECTION

Nordost 93 Bartzak Drive Holliston MA 01746 USA

Tel: +1 508 893 0100 Fax: +1 508 893 0115 Email: info@nordost.com Website: www.nordost.com

